



**NOTE:**  
 Rating: DC 12V 50mA  
 Operating Force: 200±100gf  
 Lifetime: 10,000 Cycles

PAPT NO	L
SK-3390A-L0	1.0
SK-3390A-L1	1.5
SK-3390A-L2	2.0

ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	3	Brass (0.30t)	ag Plated	—
④	Contact spring	—	1	Phosphor branze	ag Plated	—
③	Base	—	1	Lcp	Black	—
②	Cover	—	1	Sus	Natural	—
①	Keystake	—	1	Pa46	Black	—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					X.X	±0.2mm	DWN	DATE	VIEW:	SLIDE SWITCH		
ΔX					X.XX	±0.1mm	CHKD	DATE	UNIT: mm	PART NO.:		
ΔX					X.XXX	±0.05mm	APPD	DATE	SIZE: A4	DWG NO.: SK-3390A-X		
REVISIONS							UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO., LIMITED		
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn										WEIGHT	SHEET	REVISION
										1.0g	1/1	A0