

PANEL CUT-OUT		
Z	Y	X
0.70~1.25	12.90~13.10	18.9~19.1
1.25~2.00	12.90~13.10	19.1~19.2
2.00~3.00	12.90~13.10	19.3~19.4

NOTES:

1. Rating:

CQC 6A 250VAC
 6(8)A 250VAC
 8A/128A 250VAC T105/55
 UL CUL

10GPA 125VAC

6GPA 250VAC T105/55

VDE ENEC 6(4)A 250VAC T85/55

KC 6(4)A 250VAC T85/55

2. Circuit Diagram: 3P ON-OFF

3. Terminal Strength: $\geq 80N$

4. Electrical life: ≥ 10000 cycles



5. Withstand Voltage: Withstand Voltage: 1500VAC 1min
 Terminals to Button: 3000VAC 1min

6. Leakage Current: 1mA

7. Current resistance: $\leq 50m\Omega$ (initial)

8. Insulation resistance: $\geq 100M\Omega$

9. Body Material: NYLON 66 94V-2~0



A4				普通公差:	LECI 乐磁电子有限公司 LECI ELECTRONICS CO., LTD								
A3				COMMON TOLERANCE:									
A2				UP TO 5	± 0.20	单位	mm	投影		品名	跷板开关	比例	Free
A1				ABOVE 5 TO 30	± 0.30	绘图	周金勇	核对	梁金勇	型号	RS601		
				ABOVE 30	± 0.50	DRAWN BY		CHECKED BY		图号			
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	$\pm 5^\circ$	日期	2015.09.02	核准	周培雷	DWG NO.	RS601B-101N011RB		