

CK45-R3DD152K-GRA

--- Disc Type Capacitors with Lead ---



Application & Main Feature


Commercial Grade (Low Dissipation)

Series

CK45-RR

Dimensions

D	12.0mm Max.
T	5.0mm Max.
F	7.5mm +/-1.5mm
d	0.6mm +/-0.05mm
ℓ	21.0mm Min.



Temperature Characteristic

R(+15,-30%)

Rated Voltage

2000Vdc

Withstanding Voltage

4000Vdc

Capacitance

1.5nF

Capacitance Tolerance

+/-10%

Dissipation Factor

0.2% Max.

Insulation Resistance

10000Mohm Min.


AEC-Q200

Not Applicable


Lead Length / Package Type

25mm for Bulk

|Z| vs. Freq. Characteristic



Temperature Characteristic



Max. Allowable Voltage

