


**NOTES:**

- Current Rating: 1AMP
- Contact Resistance: 20mΩ max
- Withstand Voltage: 500V AC/DC
- Insulation Resistance: 1000MΩ min
- Operation Temperature: -40°C to +105°C
- Contact Material: Brass
- Contact plating: Au or Sn Over Ni
- Insulator Material: PA9T+30%GF(UL94V-0)

## Ordering Information

3130-XX M XX B K00 X 1

- |             |                   |                 |                 |
|-------------|-------------------|-----------------|-----------------|
| No. of Pins | Contact Plating   | Color Insulator | Packing         |
| 10 34       | G0=Gold Flash     | B=Black         | A=Tray          |
| 14 40       | G1=3μ"Gold        | U=Blue          | T=Tube          |
| 16 44       | G2=5μ"Gold        | W=White         | P=Tube+CAP      |
| 20 50       | G3=10μ"Gold       |                 | R=Tube&Reel+CAP |
| 24 60       | G4=15μ"Gold       |                 |                 |
| 26 64       | G5=30μ"Gold       |                 |                 |
| 30 80       | S0=Gold Flash/Tin |                 |                 |
| 32 100      | S1=3μ"Gold/Tin    |                 |                 |
|             | S2=5μ"Gold/Tin    |                 |                 |
|             | S3=10μ"Gold/Tin   |                 |                 |
|             | S4=15μ"Gold/Tin   |                 |                 |
|             | S5=30μ"Gold/Tin   |                 |                 |
|             | SN=Tin            |                 |                 |



C783830

SECTION A-A

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A2	2012/08/30	Modify CAP		X.X	TsingSn	2012/08/30	mm		3130-XXMXXBK00X1	1.27 BOX HEADER SMT H=4.90	Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com
A1	2010/09/30	Change drawing		X.XX	CHECK	DATE	inch	A4				
A0	2008/04/25	NEW		X.XXX		DATE	SHEET	1/1				
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	APPROVE	DATE	PROJ.		Customer NO.			
				± 3'								



Http: www.wcon.com