




NOTES:

- Current Rating: 1.0AMP
- Contact Resistance: 20mΩ Max
- Withstand Voltage: 500V AC/DC
- Insulation Resistance: 1000MΩ Min
- Operation Temperature: -40°C to +105°C
- Contact Material: Phosphor Bronze
- Contact plating: Au Or Sn over Ni
- Insulator Material: PBT+30%G.F UL94V-0

Ordering Information

No. of Pins	Contact Plating	Color Insulator
06P 26P	S0=Gold Flash/Ni	B=Black
08P 30P	S3=10u"Gold/Ni	G=Grey(427C)
10P 34P	S4=15u"Gold/Ni	E=Grey(413C)
12P 36P	S5=30u"Gold/Ni	
14P 40P	SN=Tin	
16P 44P		
18P 50P		
20P 60P		
22P 64P		
24P		

Item	Pitch	Mating
Standard	2.00	3121
Alternate		



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIV	TOL	APPROVE	DATE	SHEET	PROJ.	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A0	2012/10/10	NEW					2012/10/10	1/1		5223-XXYPXXBW01	2.00 IDC SOCKET WITH BUMP (T-TYPE)	Http: www.wcon.com	Tel: +86 512 57468408
OPERATION	SCALE	FIT	UNIT	DATE	DATE	CHECK	DATE	SIZE	PROJ.	Customer NO.	WCON-Dongguan	WCON-Kunshan	
XX	±0.40		mm	JYHuogng	2012/10/10			A4			Tel: +86 769 85358920	Tel: +86 512 57468408	
X.XX	±0.25										Fax: +86 769 85358915	Fax: +86 512 57468468	
X.XXX	±0.15										E-mail: sales@wcon.com	E-mail: sales@wcon.com	
Angle	± 3°												

