






CIRCUIT



P.C.B.LAYOUT

- Typical Specifications
1. Rating : DC 12V 50mA
 2. Operating Force : 250 ± 50 gf
 3. Contact Resistance : 100mΩMAX
 4. Life : 100,000 Cycles Min
- 注: LED颜色可以选配

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30~ø1.1 10~ø30 5~ø10 ~5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE	±2°	DRAWING NO.	SHEET	
	A		NEW										1 OF 1	
DRAWN							J.X.Zhang	DATE		2013/11/11		TITLE: LED Tact Switch		
CHECKED								DATE				PART NO. K6-6064A		
APPROVALS								DATE				SCALE: 1:1		
ITEM							Terminal	MATERIAL		Phosphor bronze		Ag Plating		
PART NAME							Housing	MATERIAL		Nylon		Black		
TER'NO.							QTY.	MATERIAL		FINISHING		REMARK		
APPROVALS							DATE		ELECTRONICS CO.,LTD		PROJ:			