



P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



Model NO	PJ-2040-A	PJ-2040-B
	PJ-2040B-A	PJ-2040B-B
Schematic		
Model NO	PJ-2040-C	PJ-2040-D
	PJ-2040B-C	PJ-2040B-D
Schematic		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																
	A		NEW																																																																			
<table border="1"> <tr> <td>② Terminal</td> <td>5</td> <td>Phosphor bronze</td> <td>Au Plating</td> </tr> <tr> <td>① Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER'NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2">DATE</td> <td colspan="3">TITLE: PHONE JACKES</td> </tr> <tr> <td colspan="2">DRAWN J.X.Zhang</td> <td colspan="2">2013/11/11</td> <td colspan="3">ELECTRONICS CO.,LTD</td> </tr> <tr> <td colspan="2">CHECKED</td> <td colspan="2"></td> <td colspan="3">PART NO. PJ-2040</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2"></td> <td colspan="3">SCALE: 1:1</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td colspan="2">30^{+0.15} 10^{-0.30} 5^{-0.10}</td> <td colspan="2">±0.30 ±0.20 ±0.15</td> <td>ANGLE</td> </tr> <tr> <td colspan="2"></td> <td colspan="2">~ 5</td> <td colspan="2">±0.10</td> <td>±2°</td> </tr> <tr> <td colspan="2"></td> <td colspan="2"></td> <td colspan="2">DRAWING NO.</td> <td>PROJ. SHEET 1 OF 1</td> </tr> </table>							② Terminal	5	Phosphor bronze	Au Plating	① Housing	1	Nylon	Black	ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE		TITLE: PHONE JACKES			DRAWN J.X.Zhang		2013/11/11		ELECTRONICS CO.,LTD			CHECKED				PART NO. PJ-2040			APPROVALS				SCALE: 1:1			TOLERANCES ARE		30 ^{+0.15} 10 ^{-0.30} 5 ^{-0.10}		±0.30 ±0.20 ±0.15		ANGLE			~ 5		±0.10		±2°					DRAWING NO.		PROJ. SHEET 1 OF 1
② Terminal	5	Phosphor bronze	Au Plating																																																																			
① Housing	1	Nylon	Black																																																																			
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																
APPROVALS		DATE		TITLE: PHONE JACKES																																																																		
DRAWN J.X.Zhang		2013/11/11		ELECTRONICS CO.,LTD																																																																		
CHECKED				PART NO. PJ-2040																																																																		
APPROVALS				SCALE: 1:1																																																																		
TOLERANCES ARE		30 ^{+0.15} 10 ^{-0.30} 5 ^{-0.10}		±0.30 ±0.20 ±0.15		ANGLE																																																																
		~ 5		±0.10		±2°																																																																
				DRAWING NO.		PROJ. SHEET 1 OF 1																																																																