



SPECIFICATIONS

- 1.RATING: DC30V 1.0A
- 2.MECHANICAL LIFE: 10,000 CYCLES.
- 3.PACKAGING: 1000PCS/REEL

| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |
|------|-----------|---------|------|-----------------|-----------|--------|
| ③ | Shell | --- | 1 | Phosphor Bronze | Sn Plated | --- |
| ② | Contact | --- | 5 | Phosphor Bronze | Au Plated | --- |
| ① | Housing | --- | 1 | LCP | Black | --- |

| APPROVALS | | DATE | TITLE: | |
|-----------|---------|-----------|---------------------|--|
| DRAWN | JKUN.LU | 2014/9/29 | USB CONNECTOR | |
| CHECKED | | | ELECTRONICS CO.,LTD | |
| APPROVALS | | | | |

| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. | TOLERANCES ARE | ANGLE | UNIT: | SCALE: | PROJ: | SHEET |
|---------|------|-------|--------------|---------|--------|--------|----------------|-------|-------|--------|--------------|--------|
| | A | | NEW | | | | 30~0.1± | ±2° | mm | 1:1 | U-F-M5DS-Y-3 | 1 OF 1 |
| | | | | | | | 10~0.30 | | | | | |
| | | | | | | | 5~0.10 | | | | | |
| | | | | | | | ±0.20 | | | | | |
| | | | | | | | ±0.15 | | | | | |