


1		2		3		4		5		6	
PRODUCT NO.	RoHS compliant							REV.	ECN NO.	DR	DATE
DSWB02LHGETB											


Note:

- All dimensions are in millimeters.
- General tolerance: $\pm 0.2\text{mm}$.
- Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
- Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC
 - Contact Resistance: 100 m Ω Max. at initial.
- Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 2.0mm.
 - Operation Temp: -20°C to 70°C.
 - Storage Temp: -40°C to 85°C.



DS WB 02 L H G E T B

- [Packing: T=Tube R=Reel]
- [Finish: E=1 μ "-3 μ " Gold-plated F=10 μ " Gold-plated]
- [Finish: G=Full Gold S=Contact-Gold-plated, Terminal-Tin-Plated]
- [Terminal: S=SMD type H=Straight.....]
- [Actuator: T=Tape sealed S=Low profile W/O Tape L=Extension]
- [HP=Half-Pitch IC=IC type PV=Piano type WB=WB type]



注意:

- 波峰焊: 推荐焊锡温度在270°C \pm 5°C, 浸锡时间为5~6秒钟。
- 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒钟。
- 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
- 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY		东莞市广誉实业有限公司 DongGuan Kingtek Industrial Co., Ltd.	
LINER	ANGLES	PROJECTION		TITLE	
.0 \pm 0.30	0. \pm 1'	[Symbol]		BY DSWB SERIES PITCH 2.54mm	
.00 \pm 0.20	.0 \pm 0.5'			PRODUCT FAMILY DSWB SERIES	
.000 \pm 0.10	.00 \pm			PRAT NO. DSWB02LHGETB	
DESIGN	LU ER XIN	2013/07/02		FILE NO. DSWB02LHGETB-A	
DRAWING				SIZE A4	
CHECK				UNIT mm	
APPRO.				SCALE FIT	
				SHEET 1 OF 1	
				REV. A	