



DIM. A = 2.50 X No. of Spaces  
 DIM. B = DIM. A + 5.00  
 DIM. C = DIM. A + 3.60

\* Available in 2 through 15 Citcuits

Material:

- \* Material: Nylon 46 UL 94V-0
- \* Contact: Brass, round pins

Ordering Code:

CI25 \*\* P 1 V \* 0 -LF  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② No. of Circuits
- ③ Contact type: P= Pin header
- ④ Plating option:  
 1 = 3.05 $\mu$ m(120 $\mu$ ) Matte Tin  
 over 0.76 $\mu$ m(30 $\mu$ ) Nickel
- ⑤ Tail Style: V= Straight
- ⑥ Color: 0=Nature ,1=Black ,3=Red
- ⑦ Other Option: 0= Standard
- ⑧ LF= For Lead Free IR Processes

Recommended P.C. Board Layout

RoHS Compliant

					DATE	UNIT: mm / inch	TITLE: 2.50MM(.098") STRAIGHT HEADERS	瀚荃股份有限公司 CviLux Corporation				
			DRAWN BY:	Jim	08/17-06'	TOLERANCE UNLESS OTHERWISE SPECIFIED					MATERIAL:	
			ENGINEER:	Eisley	08/24-06'	.X ± 0.30/.012	.X* ± 1'	FINISH:	DRAWING NO.	CI2516SA	PART NO.	CI25**P1V*0-LF
			CHECKED BY:	David	08/24-06'	.XX ± 0.20/.010	.X* ±		SCALE	3 / 1	SHEET	1 OF 1
SYM	NAME	DATE	REVISIONS	APPROVED BY:	David	08/24-06'	.XXX ± 0.10/0.04	.XX* ±				