


Material: Glass filled polyester UL 94V-0



Circuits	Dimension
	A
6	12.2(.480)
8	14.7(.579)
10	17.3(.681)
12	19.8(.780)
14	22.3(.878)
16	24.9(.980)
20	30.0(1.181)
24	35.0(1.378)
26	37.6(1.480)
30	42.7(1.681)
34	47.7(1.878)
36	50.2(1.976)
40	55.4(2.181)
44	60.4(2.378)
50	68.1(2.681)

Ordering Code:

CA21 ** SR 100
 ① ② ③ ④

- ① Series No.
- ② No. of Circuits
- ③ SR= Strain-Relief
- ④ Color: 100= Black

RoHS Compliant

④	Yushu	12/12-19'	ECRT119066/ECNT120007		DATE	UNIT: mm / inch	TITLE:	瀚荃股份有限公司 CviLux Corporation
③	Ken	2/12-19'	ECNT119043	DRAWN BY:	Yushu	1/9-20'	2.54MM(.100") STRAIN RELIEF	
②	Ken	3/29-17'	ECRB116097/ECNT117076	ENGINEER:	Sun	1/13-20'	MATERIAL:	DRAWING NO. CA2102SI PART NO. CA21**SR100
①	Sandy	5/03/05'	ECN05147/ECR05039-0	CHECKED BY:	Eisley	1/20-20'	FINISH:	
SYM	NAME	DATE	REVISIONS	APPROVED BY:	Eisley	1/20-20'	SCALE	3 / 1 SHEET 1 OF 1



TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X ± 0.30/.012	X.* ± 1*
.XX ± 0.20/.008	.X.* ±
.XXX ±	.XX.* ±