







SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 30mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PBT
 Max. Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)




Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Ordering Information

35112 XX B M R XX BNA2

No. of Pins: 16P, 20P, 32P, 44P, 48P, 64P
 Contact Type: M=Male
 Contact Plating: G0: Gold Flash, S2: 1.5U" Gold, S3: 2U" Gold, S4: 3U" Gold, S5: 5U" Gold, S0: Gold Flash/Tin, SN: Tin



| Dimension antitheses list | |
|---------------------------|------|
| ITEM | A |
| Standard | 3.90 |
| Alternate | |

| OPERATION | | DRAW | | SCALE | | FIT | | TITLE: | |
|--------------------------|------------|-------------|----------|-------|----|-------|-----|----------|------------------|
| OPERATION | ±0.30 | YUSheng | 14.09.16 | UNIT | mm | UNIT | A4 | PART NO. | 35112XXBMRXXBNA2 |
| X:XX | ±0.20 | CHECK | | SIZE | | SHEET | 1/1 | | |
| X:XXX | ±0.10 | APPROVE | | SHEET | | PROJ. | | | |
| Angle | ±3° | | | | | | | | |
| DIM | TOL | | | | | | | | |
| CHANGE | | | | | | | | | |
| MODIFICATION DESCRIPTION | | | | | | | | | |
| DATE | | | | | | | | | |
| REV | | | | | | | | | |
| A0 | 2012.03.28 | NEW DRAWING | | | | | | | |
| B | 2014.09.16 | 增加山标识 | | | | | | | |
| A | | | | | | | | | |

JILIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

欧式插座 公座 90度 2xNPIN 成品系列图