







**SPECIFICATIONS**

Rated Current: 3.0AMP  
 Contact Resistance: 30mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass  
 Contact Plating: Au or Sn Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PBT  
 Max. Processing Temp: 180°C for 30-60 seconds  
 (200°C for 10 seconds)

注明: 带号码球的为重点尺寸



Dimension antitheses list	
ITEM	A
Standard	4.00
Alternate	

**Ordering Information**

35113 XX C F S S0 BNA1

No. of Pins 30~96P  
 Contact Type F=Female  
 Contact Plating G0:Gold Flash  
 S2:2U" Gold  
 S3:10U" Gold  
 S4:15U" Gold  
 S5:30U" Gold  
 S0:Gold Flash/Tin  
 SN:Tin

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE
A0	2012.04.10	NEW DRAWING		X:XXX	±0.10	CHECK
				Angle	±3°	

OPERATION	DRAW	SCALE	FIT	SHEET	PROJ.	TITLE:
X:XX ±0.30	YYuSheng	UNIT	mm	A4	1/1	PART NO. 35113XXCFSS0BNA1
X:XX ±0.20	CHECK	SIZE				DIN41612(欧式插头) 3xNpin 直母排中间1排
X:XXX ±0.10	APPROVE	SHEET				

**JILIN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892