





REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	17. 12. 26	FUYONG. LIU
A1	统一料号	18. 11. 29	Mark
A2	增加防水圈	19. 07. 19	Mark



- 技术要求:
- 1 电气特性: 使用矢量网络分析仪100%测试。
 - 1.1 特性阻抗: 50Ω;
 - 1.2 适用频率范围: 824MHz-960MHz & 1710MHz-1990MHz, VSWR < 2.5;
 - 2 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
 - 3 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
 - 4 环保要求: 产品及其使用之物料皆需要符合RoHS要求。
 5. 50 PCS/袋, 成品1000 PCS装一箱, 硅胶圈1000 PCS一包放在纸箱内最上层。

No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
6	2LC15S-401	硅胶圈 0D9.6*0D1.8*0D6.0 黑色O型	1	---
5	2SBKG1400	天线杆套, 12.00*180.00, TPEE, 黑色	1	---
4	2YG012	铜管0D7.0*120*0D6.75mm, 材质黄铜	1	---
3	2TA040BK1-030	热缩套管, EVA, 4.00*130.00, 黑色	1	---
2	2YT020	天线振子, 弹簧, 12.00*147.78, 黄铜除油	1	---
1	2LC15PM015	SMA公头公针, 直头, 11.80*118.00, 黄铜镀镍	1	---

GENERAL TOLERANCE:
 LINEAR:
 X ±0.20
 X.X ±0.15
 X.XX ±0.05
 X.XXX ±0.01
 ANGLE:
 X° ±4.00°
 X.X° ±3.00°
 X.XX° ±2.00°
 X.XXX° ±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司

FILE NAME: 产品图 TITLE: 射频天线组件
 直连式外置天线, G14黑色, 铜管+弹簧,
 SMA公头公针, 总长80mm (GSM)

ENG/DATE: FUYONG.LIU/17.12.26
 CHE/DATE: P/N: HJ-GSM-SMA

APP/DATE: UNIT: mm SCALE: 1:1 REVISION: A0 SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □ HF; □ SONY SS-00259; □ OTHERS
 *NO USING ESTRICTED AND BANNED SUBSTANCE