




REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A0			The first edition released	2017.06.28	SQL
A1			统一料号	2018.11.21	Mark



- 备注:
1. 线材表面不能出现刮花，剥线沾锡不能有大头和破洞等等；
 2. SMA接头不能有假焊和短路不良，PIN针和接头的绝缘体公差为±0.2mm
 3. 线材与接头保持力：4kgf(Min), 线材与端子保持力：1.3kgf(Min);
 4. 带“(xx)”尺寸为FAI,带“*”尺寸重点尺寸,带“■”尺寸为CPK尺寸;
 5. 包装规范;25PCS/扎, 2扎/包.



7	2LC15S-302	螺母	H8.0*2.00, C3604 镀金	1
6	2LC15S-201	华司	OD10.2*1.1, C3604 镀金	1
5	2LM10P113210	I-PEX	1.13 I-PEX镀金	1
4	2TA020BK1-015	热缩套管	OD2.00*15mm黑色热缩管收缩比例2:1	1
3	2LC15SF344-7	SMA后塞	OD:4.50*L1.80+5.0*OD:2.5,穿线孔, 1.25+0.05-0.0, 适配于1.13线	1
2	2LC15SF344-1	SMA	SMA母头母针 H8.0*L18.30, 牙长16, 镀金	1
1	2C5M11311LG1	CABLE	OD1.13浅灰色银锡线, L=119mm	1
NO	P/N	PART NAME	DESCRIPTION	Q'TY

H133/H384

DIM	TOL	DIM	TOL
X.	±0.30	X'	±4.0'
X.X	±0.20	X.X'	±3.0'
X.XX	±0.10	X.XX'	±2.0'
X.XXX	±0.05	X.XXX'	±1.0'

HJ-Tech		东莞市皇捷通讯科技有限公司	
DRAW NO.	DATE	DRAW NAME:	
DESIGN:	SQL	1.13浅灰银锡线, P1端焊SMA母头母针16牙长镀金, P2端铆接MHF-1-PLUG, 裁线长119mm	
CHECK:		FILE:	P/N NO.
APPROVED:		MODEL:	HJ-IPEX1-SMA-RG1.13-119mm
REV. A0	SCALE N/A	UNIT:	SHEET:
		mm	N/A

COPLIANCE WITH THE REQUIEMENT RoHS HF SONY00259 OTHER

* NO USING RESTRICTED AND BANNED SUBSTANCE