



REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	19.05.04	Mark



- 技术要求:
- 电气特性: 使用矢量网络分析仪100%测试。
特性阻抗: 50Ω; 适用频率范围: 2.4GHz-2.5GHz; 驻波比: 最大2.00。
 - 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
 - 外观检验: 目视全检。
产品外观洁净、规整; 表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
 - 包装规范: 1PCS/扎, 20扎/袋, 即20PCS/袋, 热熔机封口。
 - 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

5	2MH039	L30.0*W13.6*T3.5mm, EVA+双面背胶	1	—
4	2MH046	支撑泡棉L7.5*W7.5*4.5mm	1	—
3	2YC008	SUS304 镀镍 L30.0*W11.0*H5.2*T0.30mm, 长振子	1	—
2	2LM10P113210	MHF-1-PLUG FOR OD1.13 CABLE	1	—
1	2C5M11312BK1	微细同轴电缆, OD1.13双锡黑色	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q'TY	REMARKS

GENERAL TOLERANCE:
LINEAR:
X ±1.00
X.X ±0.50
X.XX ±0.30
X.XXX ±0.20
ANGLE:
X° ±4.00°
X.X° ±3.00°
X.XX° ±2.00°
X.XXX° ±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司

FILE NAME: 产品图 TITLE: 射频天线组件
3.0426.02340 内置天线, 1.13双锡黑色,
P1端焊接钢片天, P2端铆接MHF1 PLUG, 裁线长L=800mm

ENG/DATE: Mark/19.05.04
CHE/DATE: P/N: HJ-IPEX1-RG1.13-800mm

APP/DATE: UNIT: mm SCALE: 1:1 REVISION: A0 SHEET: 1/1

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS H260
*NO USING ESTRICTED AND BANNED SUBSTANCE