






RoHS Compliant Customer Drawing

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

SPECIFICATION

MATERIAL

Housing:PPA+45%GF/PBT UL94V-0 贝吉色

Contacts:PhosPhor Bronze

CONTACT PLATING

G=GOLD FLASH PLATED ALL OVER, Ni UNDER PLATED ALL OVER.

T=TIN PLATED ALL OVER, Ni UNDER PLATED ALL OVER.

S=GOLD FLASH PLATED ON CONTACT AREA, TIN

PLATED ON SOLDER TAIL, Ni UNDER PLATED ALL OVER.

A=5u" (Selective)

R=3u" (Selective)

B=10u" (Selective)

P=8u" (Selective)

C=15u" (Selective)

E=2u" (Semi-Gold Matte Tin)

D=30u" (Selective)

F=3u" (Semi-Gold Matte Tin)

ELECTRICAL

Current rating: 3 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000 MΩ min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -40° C TO +105° C

Part no. A03 E - 064 F X S 0001
 1 2 3 4 5 6 7

1. SERIES NO.

5. CONTACT AREA PLATING:
SEE SPECIFICATION

2. TYPE:

E=Customer standards

6. FUNCTION OPTION:
S-STRAIGHT

3. CONTACT NUMBER

4. CONTACT TYPE:

F=Female

7. PROCESS OPTION:
Water code

公差一览表

TOLERANCE UNLESS OTHERWISE

nextion®
CONNECTOR





诺凌电子有限公司

NOXTLON ELECTRONIC CO.,LTD

X.	±0.35	X*.	±5°	单位 UNITS	mm	制图 DRAWING	姚登攀	产品名称 TITLE	欧式插座 128PIN转64PIN 直母 A型
.X	±0.30	.X*.	±2°	角法 VIEW		设计 DESIGN	姚登攀		
.XX	±0.25	.XX*.	±1°	比例 SCALE	1:1	审核 CHECK		产品料号 PART NO.	A03E-064FXS0002
.XXX	±0.02	.XXX*.	±0.5°	版本 VER	A0	核准 APPD		图号 DRAW NO.	A03E-064FXS0002-A0
DATE	2018. 04. 23								

RoHS Compliant Customer Drawing

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATION

MATERIAL

Housing: PPA+45%GF/PBT UL94V-0

Contacts: Brass

CONTACT PLATING

G= GOLD FLASH PLATED ALL OVER, Ni UNDER PLATED ALL OVER.

T= TIN PLATED ALL OVER, Ni UNDER PLATED ALL OVER.

S= GOLD FLASH PLATED ON CONTACT AREA, TIN

PLATED ON SOLDER TAIL, Ni UNDER PLATED ALL OVER.

A=5u" (Selective) R=3u" (Selective)

B=10u" (Selective) P=8u" (Selective)

C=15u" (Selective) E=2u" (Semi-Gold Matte Tin)

D=30u" (Selective) F=3u" (Semi-Gold Matte Tin)

ELECTRICAL

Current rating: 3 Amps .

Contact resistance: 20 mΩ initial

Insulation resistance: 1000MΩ min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -40° C TO +105° C

Part no. A03 E - 064 M X S 0006
 1 2 3 4 5 6 7

1. SERIES NO.

2. TYPE:

A=Standard

3. CONTACT NUMBER

4. CONTACT TYPE:

M=Male

5. CONTACT AREA PLATING:


SEE SPECIFICATION

6. FUNCTION OPTION:

S=STRAIGHT

7. PROCESS OPTION:

Water code



PCB LAYOUT(RECOMMENDED)
(TOP VIEW TOL. :±0.05)

公差一览表				nextion®		诺凌电子有限公司			
TOLERANCE UNLESS OTHERWISE				CONNECTOR		NOXTLON ELECTRONIC CO.,LTD			
X.	±0.35	X°	±5°	单位 UNITS	mm	制图 DRAWING	蒋伟	产品名称 NAME	欧式插座 128PIN转64PIN 直针 A型
.X	±0.30	.X°	±2°	角法 VIEW	⊕	设计 DESIGN	蒋伟	产品料号 PART NO.	A03E-064MYS0006
.XX	±0.25	.XX°	±1°	比例 SCALE	1:1	审核 CHECK		图号 DRAW NO.	
.XXX	±0.02	.XXX°	±0.5°	版本 VER	A0	核准 APPD			
DATE	2017.10.23								