


1	2	3	4	5	6	7	8
REVISION		DESCRIPTION		DATE		DRAFTER	
A0		FIRST RELEASE		18.08.09		DENGJUN.TAN	



技术要求:

- 电气特性: 使用矢量网络分析仪100%测试。
特性阻抗: 50Ω; 适用频率范围: 2.4GHz-2.5GHz; 驻波比: 最大2.00。
- 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
- 外观检验: 目视全检。
产品外观洁净、规整; 表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
- 包装规范: 1PCS/扎, 20扎/袋, 即20PCS/袋, 用黑色扎带。
- 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

5	2MB020	白色底蓝色字双面背胶L38.8*W17.4*TO.15mm	1	—
4	2MH014	EVA L27.50*W5.70*T2.3*2.5mm, L15.5单面背胶	1	注意: 泡棉厚度
3	2YC003	洋白制(振子)半剪 L35.75*W17.60*TO.20mm	1	—
2	2LM10P113210	MHF-1-PLUG FOR OD1.13 CABLE	1	—
1	2C5M11312BK1	微细同轴电缆, OD1.13双锡黑色	1	依裁线图裁线
No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS

GENERAL TOLERANCE:

LINEAR:

X	±0.20
X.X	±0.15
X.XX	±0.05
X.XXX	±0.01

ANGLE:

X°	±4.00°
X.X°	±3.00°
X.XX°	±2.00°
X.XXX°	±1.00°

HJ-Tech 东莞市皇捷通讯科技有限公司

FILE NAME:	产品图	TITLE:	射频天线组件
ENG/DATE:	DENGJUN.TAN/18.08.09		钢片内置天线; OD1.13双锡黑色;
CHE/DATE:			P1端焊接P1FA; P2端铆接MHF-1 PLUG; 裁线长L=800mm
APP/DATE:		P/N:	HJ-IPEX1-RG1.13-800mm-3N0201BK-002
		UNIT:	mm
		SCALE:	1:1
		REVISION:	A0
		SHEET:	1/1

COMPLIANCE WITH THE REQUIREMENT: ■ RoHS; □ HF; □ SONY SS-00259; □ OTHERS
*NO USING ESTRICTED AND BANNED SUBSTANCE