


REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	19.03.04	MARK



技术要求:

- 特性阻抗: 50Ω;
- 适用频率范围:  
824MHz-960MHz, VSWR 3.0 max;  
1710MHz-2690MHz, VSWR 3.0 max.
- 尺寸检验:  
[\*]为FAI检测项目; \*为重点检测项目; ■为CPK管制项目.
- 外观检验: 目视全检.  
产品表面不得有刮伤、破损、脏污、异色与色差.
- 包装规范: 50PCS/袋.
- 环保要求:  
产品及其使用之物料皆需要符合RoHS要求.

8	Connector	SMA Staight plug	1
7	Antenna Base	PC, Color:Black	1
6	Cable	RG-178 Cable,	1
5	Rivet	POM, Color:Black	2
4	Antenna Base	PC, Color:Black	1
3	PCB ANTENNA	PCB FR-4	1
2	AntennaHousing (R)	PC+ABS, Color:Black	1
1	AntennaHousing (L)	PC+ABS, Color:Black	1
NO	PART NAME	DESCRIPTION	Q. TY

GENERAL TOLERANCE: LINEAR: X ±5.0 X.X ±0.50 X.XX ±0.20 X.XXX ±0.01 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司	
FILE NAME: 产品图	TITLE: 剑型4G天线(黑色), SMA公头母针 (POM 外壳)	P/N: HJ-LTE-SMA-3D2701BK07-002	
ENG/DATE: Mark/19.03.04	CHE/DATE:	UNIT: mm	SCALE: 1:1
APP/DATE:	REVISION: A0	SHEET: 1/1	

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS  
\*NO USING ESTRICTED AND BANNED SUBSTANCE