



REVISION	DESCRIPTION	DATE	DRAFTER
A0	FIRST RELEASE	18.04.27	DENGJUN. TAN
A1	统一料号	18.10.18	Mark
A2	增加背胶料号	20.06.10	Mark

技术要求:

- 电气特性: 特性阻抗:50Ω; 适用频率范围:1.92GHz-1.97GHz, 驻波比:最大2.5; 1.97GHz-2.02GHz, 驻波比:最大2.0。  
检验方法: 使用矢量网络分析仪100%测试。
- 尺寸检验: [\*]为FAI检测项目; \*为重点检测项目; ■为CPK管制项目。
- 外观要求: 产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。  
检验方法: 目视全检验。
- 包装规范: 20PCS/扎, 5扎/包, 即100PCS/包。
- 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
5	2MH045	L10.0*W8.7*H0.35mm, 双面3M 9448A背胶(特粘)	1	---
4	2YP026	PCB, T0.60*W8.70*H1.54.00, 表面黑色油墨阻焊, 焊盘OSP处理	1	---
3	2SWG2222	白外壳, L86.81*W11.95*H14.98mm, 后盖塑件	1	---
2	2SWG2211	白外壳, L86.81*W11.95*H14.98mm, 爪型塑件	1	---
1	2C5M11312BK1	微细同轴电缆, OD1.13, 双锡线, 黑色	1	---

GENERAL TOLERANCE: LINEAR: X ±0.20 X.X ±0.15 X.XX ±0.05 X.XXX ±0.01 ANGLE: X° ±4.00° X.X° ±3.00° X.XX° ±2.00° X.XXX° ±1.00°		<b>HJ-Tech</b> 东莞市皇捷通讯科技有限公司 FILE NAME: 产品图 TITLE: 射频天线组件 ENG/DATE: DENGJUN. TAN/18.04.27 CHE/DATE: . P/N: HJ-2.4G-1.13-PCB-L85MM APP/DATE: . UNIT: mm SCALE: 1:1 REVISION: A0 SHEET: 1/1	
---	--	---	--

COMPLIANCE WITH THE REQUIREMENT: ■ RoHS; □ HF; □ SONY SS-00259; □ OTHERS H410  
 \*NO USING ESTRICTED AND BANNED SUBSTANCE