



SPECIFICATIONS



1. Voltage rating: 150V AC, DC
 2. Current rating: 3A, AC, DC
 3. Withstanding Voltage: 500V AC/minute
 4. Insulation resistance: 1000M min
 5. Temperature range: -25 °C - +85 °C
 6. Contact resistance: 20m max
- WAFER
 Housing Material: PA4T UL 94V0
 Pin Material: Phosphor Bronze or Brass
 Contact Area Plating: Plated Tin or Plated Gold
 Mates with :P1503 series Housing
 Poles: 02-12P
 Part No.: M1503RS-xx-BK

Pin位数


Poles	Dimensions(mm)			
	A	B	C	D
02	1.50	6.75	2.85	
03	3.00	8.25	4.35	
04	4.50	9.75	5.85	
05	6.00	11.25	7.35	3.00
06	7.50	12.75	8.85	3.00
07	9.00	14.25	10.35	4.50
08	10.50	15.75	11.85	6.00
09	12.00	17.25	13.35	7.50
10	13.50	18.75	14.85	9.00
11	15.00	20.25	16.35	10.50
12	16.50	21.75	17.85	12.00



02P~04P Single Hole
 Scale 1:0.7



DETAIL B
 SCALE 1:1



此面不能有毛刺

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1	
				X.	±0.30	X°	±5°			CHKD	DATE	2010. 4. 12
				.X	±0.20	.X°	±2°	APPD	PRODUCT NAME	1.50mm Crimp Style Connectors	UNITS	mm
				.XX	±0.08	.XX°	±1°	VIEW	PART. NO.	M1503RS-xx-BK	SCALE	1:1
A0 VER	MODIFICATION			DATE	DATE						DWG NO.	009