



SPECIFICATIONS

1. Voltage rating: 150V AC, DC
2. Current rating: 3A, AC, DC
3. Withstanding Voltage: 500V AC/minute
4. Insulation resistance: 1000M min
5. Temperature range: -25 ° C +85 ° C
6. Contact resistance: 20m max

TERMINAL

Material: Phosphor Bronze
 Finish: Plated Tin or Plated Gold
 Applicable wire: AWG#24-#28
 Insulation O.D.: 1.10mm(Max)
 Used in : P1503 SERIES HOUSING
 Qty/Reel: 10000PCS
 Part No.: T1503PS-00

00=镀金 2=镀锡

WWW.XFCN.COM

| | | | | | | | | | | | |
|-----------|--------------|--|------|----------------------------|-------|-------|--------|---|--------------|-------------------------------|------|
| | | | | TOLERANCE UNLESS OTHERWISE | | DRAWN | CK tan | XFCN 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD. | | SHEET | 1/1 |
| | | | | X. | ±0.30 | X° | ±5° | | | CHKD | DATE |
| | | | | .X | ±0.20 | .X° | ±2° | APPD | PRODUCT NAME | 1.50mm Crimp Style Connectors | |
| | | | | .XX | ±0.08 | .XX° | ±1° | VIEW | PART. NO. | T1503PS-00 | |
| | | | | .XXX | ±0.03 | .XXX° | ±0.5° | | | SCALE | 1:1 |
| | | | | | | | | | | DWG NO. | 009 |
| A0 VER | MODIFICATION | | DATE | | | | | | | | |