



Circuit Diagram



P.C.B layout



NOTE:

- 1. Rating: DC30V 0.1A
- 2. OP: 8.70±0.8
- 3. Operating force: 30±15gf
- 4. Mechanical Life: 3,000,000

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑦	Shrapnel	—	1	Beryllium Copper	—	—
⑥	Contact	—	1	Ag	—	—
⑤	Lever	—	1	Stainless Steel	—	—
④	Terminal	—	3	Brass(0.50t)	Plating silver	—
③	Housing	—	1	PBT	White	—
②	Knob	—	1	POM	Green	—
①	Cover	—	1	PBT	Black	—

APPROVALS		DATE	HRO 韩荣® ELECTRONICS CO.,LTD			
DRAWN	J.X.Zhang	2013/6/4	TITLE:	MICRO SWITCHS		
CHECKED			PART NO.	K9-1267H-13-G		
APPROVALS			TOLERANCES ARE	ANGLE	UNIT: mm	SCALE: 1:1
			30~以上 ±0.30	±2°		PROJ:
			10~30 ±0.20		DRAWING NO.	SHEET 1 OF 1
			5~10 ±0.15			
			~ 5 ±0.10			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			