


Notes :

- \* Insulation: Nylon 6T UL 94V-0, Color Nature
- \* Contact : Phosphor Bronze
- \* Fixed Tab : Brass with Matte Tin Plated
- \* Recommended mating part:  
Housing: CI44\*\*S0000-L  
Terminal: CI44T011PP0
- \* For Lead-Free IR Reflow process

**ORDERING CODE:**

CI44 \*\* M \* H \*\* -NH  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.:
- ② No. of circuits: 02 TO 15
- ③ Contacts type: M= SMT
- ④ Plating option:  
1= Matte Tin Plated over Nickel  
2= Gold flash plated over Nickel
- ⑤ Tail style: H= Right angle
- ⑥ Option: 00= Standard(Tube packing)  
R0= Tape & Reel packing
- ⑦ Other option:  
-NH=For Lead Free IR Processes and Halogen-Free



A = 1.25 x No. of Spaces  
B = A + 6.1  
C = A + 1.9

\* Available in 2 through 15 circuits

Halogen-Free

Lead Free Process

RoHS compliant

CVILUX CORP  
2019.08.22  
ISSUED

5	Sun	8/15-19'	ECNT119210	DATE	UNIT: mm / inch	TITLE: 1.25MM(.049") RIGHT ANGLE SMT TYPE HEADER	 瀚荃股份有限公司 CviLux Corporation
4	Karen	12/09-14'	ECNT114252/ECRT114090	DRAWN BY: Sun	8/15-19'	TOLERANCE UNLESS OTHERWISE SPECIFIED	
3	Ellie	9/24-14'	ECNT114210	ENGINEER: Sun	8/15-19'	.X ± 0.25/.010    X.* ± 1'	
2	Enya	7/26-12'	ECN12176-0 / ECR12061-1	CHECKED BY: Eisley	8/16-19'	.XX ± 0.15/.006    .X.* ±	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	8/16-19'	.XXX ± 0.08/.003    .XX.* ±	
DRAWING NO. CI4447SF    PART NO. CI44**M*H**-NH							SCALE 5 / 1    SHEET 1 OF 2

