



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.20
Pt	±0.08	±0.10	±0.10	±0.15	+0.2 -0.4
W	±0.08	±0.10	±0.10	±0.20	+0.2 -0.4
M	±0.08	±0.12	±0.12	±0.20	±0.30
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
<b>Ft±0.01</b>	0.060
<b>St±0.01</b>	0.225

Tolerance of Cutting Tilt

RoHS Compliant

**UL Style : 20706**

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCC1206T205000-300	12	1	11	50	13	1	0.7	0.035	5	5	10	10	BLUE
	FFCC0606T205000-300	6	1	5	50	7	1	0.7	0.035	5	5	10	10	BLUE

4						DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation
3			DRAWN BY: Sally		5/23-08'	TOLERANCE UNLESS OTHERWISE SPECIFIED		<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T2)</b>	
2			ENGINEER: Terry		5/23-08'	.X ±	X' ± 2'	MATERIAL: SEE PRODUCT SPECIFICATION	
1			CHECKED BY: Leno		5/23-08'	.XX ±	.X' ±	CUST. CODE: 寶福新成	
SYM	NAME	DATE	APPROVED BY: William		5/23-08'	.XXX ±	.XX' ±		
REVISIONS					SCALE	1 / 1	DRAWING NO. FFCC002SF	FILE NO. T208043-2A	SHEET 1 OF 1