



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				



	Dimension
$Ft \pm 0.01$	0.060
$St \pm 0.01$	0.225


Tolerance of Cutting Tilt



UL Style : 20706 105°C 60V

RoHS Compliant

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d±2.0	
	FFCC0814T9050Z0-300	08	1.0	7.0	50	9.0	1.0	0.65	0.05	3.5	5.0	10	BLUE

4				DATE	UNIT: mm	TITLE: FLAT FLEXIBLE CABLE (TERMINAL TYPE : T9)	 瀚荃股份有限公司 CviLux Corporation	
3				DRAWN BY: long	9/4-12'	TOLERANCE UNLESS OTHERWISE SPECIFIED		
2				ENGINEER BY: long	9/4-12'	.X ±	MATERIAL: SEE PRODUCT SPECIFICATION	
1				CHECKED BY: Lian	9/4-12'	.XX ±	DRAWING NO. FFC009S1 FILE NO. T918009-4A	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Iron	9/4-12'	.XXX ±		CUST. CODE: 寶福
							SCALE	SHEET 1 OF 1