


TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.05	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				




	Dimension
Ft±0.01	0.043
St±0.01	0.225

RoHS Compliant

UL Style : 20706

Note:S1/S2<d1/d2

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±0.5	S2±0.5	d1±2.0	d2±2.0	
	FFCC0614T2030CA-300	06	1.0	5.0	30	7.0	1.0	0.65	0.05	3.0	3.0	4.0	4.0	BLUE
	FFCC2414T2030CA-300	24	1.0	23	30	25	1.0	0.65	0.05	3.0	3.0	4.0	4.0	BLUE

4					DATE	UNIT: mm	TITLE: FLAT FLEXIBLE CABLE (TERMINAL TYPE : T2)	 瀚荃股份有限公司 CviLux Corporation	
3				DRAWN BY: Fang	10/08-12	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL: SEE PRODUCT SPECIFICATION		
2				ENGINEER: Lan	10/08-12	.X ±	.X' ± 2'	DRAWING NO. FFC002SG FILE NO. T212257-4A	
1				CHECKED BY: Lian	10/08-12	.XX ±	.X' ±		
SYM	NAME	DATE	REVISIONS	APPROVED BY: Lian	10/08-12	.XXX ±	.XX' ±	CUST. CODE: 寶福	
								DRAWING NO. FFC002SG	FILE NO. T212257-4A
								SCALE 1 / 1	SHEET 1 OF 1

CviLux
2012.12.12
ISSUED