



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
Ft±0.01	0.043
St±0.01	0.225

Tolerance of Cutting Tilt

RoHS Compliant

UL Style : 20706

NOTE:S1/S2<d1/d2

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE0808T1060AA-300	8	0.5	3.5	60.0	4.5	0.5	0.3	0.05	2.0	2.0	4.0	4.0	BLUE

4				DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation				
3		DRAWN BY: June	11/12-10'	TOLERANCE	.X ±	.X' ± 2'					
2		ENGINEER: Feng	11/12-10'	UNLESS OTHERWISE SPECIFIED							
1		CHECKED BY: Iron	11/12-10'	.XX ±	.X ±						
SYM	NAME	DATE	REVISIONS	APPROVED BY: David	11/12-10'	.XXX ±	.XX ±	MATERIAL: SEE PRODUCT SPECIFICATION	DRAWING NO. FFC001SF	FILE NO.	T110515-2A
								CUST. CODE: ACL1058	SCALE 1 / 1	SHEET 1 OF 1	