



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04

Note:
1. Conductor Plated: Sn(40u"Min)

	Dimension
Ft±0.01	0.043
St±0.01	0.225

Assembled View:



UL Style : 20706 105°C 60V

RoHS Compliant

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L±2	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE10082B19B0540	10	0.5	4.5	150	5.5	0.5	0.30	0.05	4.0	4.0	8.0	8.0	Blue
	FFCE1008T215000-300-P													

4				DATE	UNIT: mm	TITLE: FLAT FLEXIBLE CABLE (TERMINAL TYPE : T2)	瀚荃股份有限公司 CviLux Corporation				
3			DRAWN BY: long	11/19-19'	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL: SEE PRODUCT SPECIFICATION					
2			ENGINEER BY: long	11/19-19'	.X ±	X' ± Z'	THIRD ANGLE DRAWING NO. T219135-4A				
1			CHECKED BY: Kenny	11/19-19'	.XX ±	X ±					
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	11/19-19'	.XXX ±	Xx ±	CUST. CODE:	SCALE	—	SHEET 1 OF 1