



**TOLERANCE:**

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
<b>Ft±0.01</b>	0.043
<b>St±0.01</b>	0.225

Tolerance of Cutting Tilt

RoHS Compliant

**UL Style :20706 105°C 60V**

**Note:S1/S2<d1/d2**

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE2009T2080CB-300	20	0.5	9.5	80	10.5	0.5	0.3	0.035	3.0	3.0	5.0	5.0	BLUE

4					DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation
3				DRAWN BY: Mei	6/10-13'	TOLERANCE UNLESS OTHERWISE SPECIFIED	<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T2)</b>	
2				ENGINEER: Lan	6/10-13'	.X ±	MATERIAL: SEE PRODUCT SPECIFICATION	
1				CHECKED BY: Lian	6/10-13'	.XX ±	CUST. CODE:	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	6/10-13'	.XXX ±		DRAWING NO. FFC002SF FILE NO. T215072-4A SCALE 1 / 1 SHEET 1 OF 1