


TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				




Tolerance of Cutting Tilt

	Dimension
Ft±0.01	0.043
St±0.01	0.225

RoHS Compliant

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0		d2±2.0
	FFCE4008T104700-300	40	0.5	19.5	47	20.5	0.5	0.3	0.05	4.0	4.0	8.0	8.0	BLUE

4					DATE	UNIT: mm	TITLE:	 瀚荃股份有限公司 CviLux Corporation
3				DRAWN BY: Marry	1/20-09'	TOLERANCE UNLESS OTHERWISE SPECIFIED	FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)	
2				ENGINEER: Qijie	1/20-09'	.X ±	X' ± 2'	MATERIAL: SEE PRODUCT SPECIFICATION
1				CHECKED BY: Qijie	1/20-09'	.XX ±	.X' ±	CUST. CODE: HL0014
SYM	NAME	DATE	REVISIONS	APPROVED BY: Jacky	1/20-09'	.XXX ±	.XX' ±	DRAWING NO. FFC001SF
								FILE NO. T109023-2A
								SCALE 1 / 1
								SHEET 1 OF 1

