


TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				




Tolerance of Cutting Tilt

	Dimension
Ft±0.01	0.043
St±0.01	0.225

RoHS Compliant

UL Style : 20706 105C 60V

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±0.5	S2±0.5	d1±1		d2±1
	FFCE4008T1150CA-300	40	0.5	19.5	150	20.5	0.50	0.3	0.05	3	3	4	4	BLUE

4				DATE	UNIT: mm	TITLE:	 瀚荃股份有限公司 CviLux Corporation	
3			DRAWN BY: long	4/23-19	TOLERANCE UNLESS OTHERWISE SPECIFIED	FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)		
2			ENGINEER: long	4/23-19	.X ±	MATERIAL: SEE PRODUCT SPECIFICATION		
1			CHECKED BY: Kenny	4/23-19	.XX ±	CUST. CODE:		
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	4/23-19	.XXX ±	.XX ±	
							DRAWING NO. FFC001SF	FILE NO. T119228-4A
							SCALE 1 / 1	SHEET 1 OF 1