



Recommend PCB layout



GT-USB-2014-CBG1

- G-Switch
- USB系列
- 系列编码
- G1=1U
- G3=3U
- G5=5U
- G15=15U
- G30=30U
- C=铜壳
- I=铁壳
- W=白色
- B=黑色
- N=其它

规格说明: Specifications: N=其它
电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN



品源科技
b-Switch

Unless otherwise specified, Tolerance:
X ±0.30
X.X ±0.20
X.XX ±0.15
X.XXX ±0.10
Angles ±3

G-Switch Electronic Technology CO., Ltd.

DESIGN	陈锋刚	DATE	2016.05.29	TITLE:	GT-USB-2014-CBG1
CHECKED		DATE		REV.:	X1
APPROVED		DATE		SCALE:	4:1
http://www.dg-switch.com				UNIT:	mm
TEL: 0769-82388879				SIZE:	A4
				SHEET:	1/1