







CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 8P8C 半沉4.6带壳双脚(有缺口)	MJ88-BX11-HLRS1-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	SIMON	2016.12.01
A02	—	整理图纸	YST	2019.07.01



MJ88-BX11-HLRS1-X

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating

X	包装方式
C	卷带包装
P	吸塑盒包装

c	SHELL	1	BRASS T=0.2mm	NI PLATING	
b	TERMINAL	8	PHOSPHOR BRONZE	AU PLATING	
a	HOUSING	1	LCP UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X : ±0.5	X : ±2°
XX : ±0.3	XX : ±1°
XXX : ±0.2	

东莞市合陵电子有限公司
 Dongguan Heling Electronic Co., LTD
 Connector

SCALE: 1/1 UNIT: mm DWG. NO.:
 SIZE: A3 PAGE: 1 OF 1 REV: A02
 APPROVED BY: XSY CHECKED BY: XSY PREPARED BY: XSY
 DICK: XSY
CUSTOMER COPY

- SPECIFICATION
- VOLTAGE RATING: 150 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE: AC1000V RMS 60s.
 - OPERATING TEMPERATURE: -40°C~+80°C