А		В	С		D		E			F		
							REV.	MODI	FICATION.	DATE	DRN	
2							01	CO2	011072	18/02/11	SF	
ł							1 1			1		
ł												
Ø10.7 −												2
						RICHCO	INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.					
							CO, IN CHCO-INC	IC. U COM 1 2	LL DIMENSIONS II ENERAL TOLERAL NLESS OTHERWISI DECIMAL PLACE DECIMAL PLAC NGULAR ±1°	NCES ±0.25 E STATED		
MATERIAL: UL94 V-2 NYLON 6/6, RMS-01* COLOUR: NATURAL						ΝΛΛΤΕΡΙΑΙ		A	NGULAK ±1	COLOUR:	ψ \frown	-
PART No.	hole Ø	PANEL THICKNESS	CABLE TIES ACCEP	PTED		See table				See tab	ble	
FTH-9-01-M	6.35±0.08	3.18 MAX.	All RG CABLE TIES UP TO SIZE RG-220/320			DESCRIPTION: FLAT TIE HOLDER				PART No: See Table		
*AVAILABLE IN UL94 V-0 BY SPECIAL ORDER TO ORDER REPLACE -01 WITH -19 0									XX-XXX	SHEET SIZE		_
						drn SF	date 18/02/11	снкр ЈК	DATE 18/02/11	scale NTS	sheet No. 1 OF 1	
А		В	С		D		E			FORM	No. 0143/00	