



A:With
 B:without

SPECIFICATION

Contact Rating:	50mA, 12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100mΩ min. 500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30°C ~ +85°C
Storage Temp:	-30°C ~ +80°C

PAPT NO	TS-3025-X-X-X
Operating Force	A: 160gf B: 260gf C: 350gf
Height	H: A: 1.5 B: 1.6 C: 1.7
Fixed column	A:With B:without

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Lcp	—	—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46	—	—

MARK	DESCRIPTION	DATE	REVISED	APPROVED	units: mm	DSND	DATE	SCALE: N/A	MODEL TYPE:
Δx					tolerance:	DWN	DATE	VIEW:	TACT SWITCH
Δx					X.X ±0.2mm	CHKD	DATE	UNIT: mm	PART NO.:
Δx					X.XX ±0.1mm	APPD	DATE	SIZE: A4	DWG NO.:
MARK					X.XXX ±0.05mm	XKB INDUSTRIAL PRECISION CO., LIMITED			TS-3025-X-X-X
UNSPECIFIED TOLERANCES						WEIGHT	SHEET	REVISION	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						1.0g	1/1	A0	