



MAPX	MODIFICATION	DATE

特性:Specifications

电气:Electrical:

1. 接触阻抗:Contact Resistance
30 milliohms MAX
2. 耐电压:Dielectric Withstanding Voltage:
500 V AC AT Sea Level
3. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

机构:Mechanical:

1. 结合力:Mating Force:
4.0KG NAX 最大4kg
2. 拔出力:Unmating Force:
0.5 KG NIN 最少0.5kg

材料:Material:

1. 塑胶:Housing:High Temperature Thermoplastic
2. 端子:Contact:Copper Alloy 铜合金
3. 外壳:Shell: Copper Alloy铁/铜合金

电镀:Finish:

1. 端子:Contact: Plated Gold in Mating Area;
Tin On Solder Tail
接触点镀金. 脚镀锡
2. 外壳:Shell:
Nickel Plating 镀镍

<p>产品图 PRODUCT CHART DWG</p>				<p>深圳市精拓金电子有限公司</p>						
<p>公差一览表 TOLERANCE UNLESS OTHERWISE</p>				单位	制图	制图料号	<p>907-111A1012D10200</p>			
X.	±0.25	X.	±5.°	UNITS	MM	DRAWING	Z-Y-B	PRODUCT PART NO.	907-111A1012D10200	
.X	±0.20	.X	±2.°	比例	1:1	审核	L-Y-J	产品名称	AF90度17.0双层半包弯脚小卷边平	
.XX	±0.15	.XX	±1.°	SCALE		核准	L-Y-J	角法	弹铁壳PBT白胶端子间距2.6	
.XXX	±0.10	.XXX	±0.5°	日期	2014.06.09	核准备	L-Y-J	角法	版本	A0
				DATE		APPD		VIEW	VER	