



D款, 正向10.6前两脚, SMT-*6.20

MAPX	MODIFICATION	DATE



NOTES:
 1.HOUSING: SEE NOTES, UL94V-0 .
 TERMINAL: SEE NOTES.
 SHELL: SEE NOTES.
 SPECIFICATION:
 1.ELECTRICAL CHARACTERISTIC:
 CONTACT RESISTANCE: $30M\Omega$ MAX
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1MIN
 INSULATION RESISTANCE: $1000M\Omega$ MIN
 2.MECHANICAL CHARACTERISTIC:
 INSERTION FORCE: 35N(3.57KGF) MAX
 EXTRACTION FORCE: 10~35N(1.02~3.57KGF)MIN
 DURABILITY: 1500 CYCLES EXTRACTION FORCE:10~35N
 5000 CYCLES MIN
 5000 CYCLES EXTRACTION FORCE:3~35N

3.ENVIRONMENTAL:
 OPERATING TEMPERATURE: $-55^{\circ}C+85^{\circ}C$
 4.Contact finish:
 01:Selective Gold Flash
 02:Selective Gold 3U"
 03:Selective Gold 5U"
 04:Selective Gold 15U"
 05:Selective Gold 30U"



产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司							
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	912-121A2026S10100		
X.	± 0.15	X.	$\pm 5^{\circ}$	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NAME	AF10.6D款前两脚无边方弹壳LCP 黑胶6.2SMT无耳朵		
.X	± 0.10	.X	$\pm 2^{\circ}$	日期 DATE	2012.09.24	核准 APPD		角法 VIEW		版本 VER	AD
.XX	± 0.05	.XX	$\pm 1^{\circ}$								
.XXX	± 0.03	.XXX	$\pm 0.5^{\circ}$								