

**GT-TC174X-HXXXX-LX**

**G-SWITCH**



**Operating Force**  
 A=160gf  
 B=250gf  
 C=320gf  
 D=100gf

**Switch Height(mm)**  
 H0065=0.65mm



**Switch lifetime (Force)**  
 L1=100,000 Cycles  
 L3=300,000 Cycles

**G-Switch Specification:**

Operating temperature range: -30°C to +85°C  
 Rating: 50mA, 12V DC  
 Insulation resistance: 100MΩ min, 100V DC  
 Dielectric strength: 250V AC for 1 min  
 Contact resistance: 100mΩ max.  
 Travel: 0.15±0.05mm



**P.C.B LAND DIMENSION**



**G-Switch Electronic (HongKong) CO.,Ltd.**

Unless otherwise specified, Tolerance:  
 X. ±0.30  
 X.x ±0.20  
 X.xx ±0.15  
 X.xxx ±0.10  
 Angles ±3°

DESIGN 陈锋枫 DATE 2019.05.29  
 CHECKED DATE  
 APPROVED DATE  
<http://www.dg-switch.com>  
 TEL: 0769-82388879

Molde code:  
 GT-TC174X-HXXXX-LX  
 REV.: X1 SCALE: 4:1 UNIT: mm  
 SIZE: A4 SHEET: 1/1