






MAPX	MODIFICATION	DATE



- Specifications:
1. Insertion force: 44.1N MAX.
 2. Withdrawal force: 9.8~39.2N.
 3. Durability: 10000 Cycles.
 4. Current rating: 0.5A
 5. Voltage rating: 40V AC MAX.
 6. Dielectric strength: 500V AC MIN. (UNMATED) 300V AC MIN. (MATED)
 7. Contact resistance: 30mΩ MAX.
 8. Insulation resistance: 100MΩ DC MIN (UNMATED) 10MΩ DC MIN (MATED)
 9. Temperature: -40°C TO +85°C
 10. All the material must accord with the RoHS.
 11. The important dimensions with "▲"



03	Terminal	C5191	19	Gold plated within connect area ,Tin plated within solder area
02	Housing	LCP	1	LCP+30%GF UL94-V0, Color is black
01	Shell	SPCC/C2680	1	Plating nickle or gold overall
序号 NO.	品名 PART NAME.	材料 MATERIAL	用量 QTY	备注说明 NOTE

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司							
公差一览表 TOLERANCE UNLESS OTHERWISE		单位	制图	制图料号	920-867A2021Y10100				
X.	±0.15	X.	±5.°	MM	Z-Y-B	PRODUCT PART NO.	920-867A2021Y10100		
.X	±0.10	.X	±2.°	比例	郭治富	产品名称	HDML 19PIN M 15.0线端A款6-1夹板式		
.XX	±0.05	.XX	±1.°	SCALE	核 准	PRODUCT NO.	1.6mm铁壳镀金LCP黑胶		
.XXX	±0.03	.XXX	±0.5°	日期	黄国荣	角法	版本	角法	A0
				DATE	2016-09-09	核 准	APPD	角法	VER