








MAPX	MODIFICATION	DATE
------	--------------	------




NOTES:
 1)MATERIAL:
 HOUSING:THERMOPLASTIC,UL 94V-0,
 COLOR:BLACK
 CONTACT:COPPER ALLOY T=0.20mm
 SHELL A:STAINLESS STEEL T=0.40mm
 SHELL B: SPCC T=0.25mm
 2)FINISH:
 CONTACT:1u" MIN GOLD PLATING ON CONTACT AREA
 G/F PLATING ON SOLDERTAILS
 SHELL: G/F PLATING ON SOLDERTAILS



Pin No.	SIGNAL
1	SCC1
2	DP1
3	DN1
4	PWR_IN_A
5	PWR_IN_B
6	DN2
7	DP2
8	ACC2
9	DETECT_1
10	DETECT_2
SHELL_A	GND
SHELL_B	GND



section
A-A



RECOMMENDED P.C.B LAYOUT(TOP VIEW)
GENERAL TOLERANCE +/-0.05

产品图 PRODUCT CHART DWG 公差一览表 TOLERANCE UNLESS OTHERWISE		深圳市精拓金电子有限公司								
X.	±0.35	X.	±5.°	单位	MM	制图	Gavin	制图料号	914-614A2024S10201	
.X	±0.30	.X	±2.°	比例	1:1	审核	郭治富	产品名称	AF苹果款15沉板1.6四脚前插后贴	
.XX	±0.20	.XX	±1.°	日期	2016-09-09	核准	黄国荣	角法	角法	
.XXX	±0.10	.XXX	±0.5°	日期	2016-09-09	APPD		版本	AD	

由Autodesk 教育版产品制作

由Autodesk 教育版产品制作