



目录 MAPX	设变内容 MODIFICATION	日期 DATE

特性: Specifications:

电气: Electrical:

- 接触阻抗: Contact Resistance:
30 milliohms MAX
- 耐电压: Dielectric With Standing Voltage:
500 V AC AT Sea Level
- 绝缘阻抗: Insulation Resistance:
1000 MEGA ohms MIN

机构: Mechanical:

- 结合力: Mating Force:
35 N MAX 最大 35 N
- 拔出力: Unmating Force:
8 N MIN 最少 8 N

材料: Material:

- 塑胶: 黑色PBT.
- 端子: Contact: C2680, T= 0.25 ± 0.01
- 外壳: Shell: SPCC, T= 0.3 ± 0.01

电镀: Finish:

- 端子: Contact: Plated Gold in Mating Area:
Tin/Lead On Solder Talls. 接触点镀金1唛, 脚镀锡100唛
- 外壳: Shell:
Nickel Plating . 镀镍80唛
额定电流2.5A, 盐雾24H, 镀锡部分12H

产品图 PRODUCT CHART DWG			
公差表 TOLERANCE UNLESS OTHERWISE			
尺寸	A	B	*C
0-5	± 0.02	± 0.05	± 0.1
5-10	± 0.05	± 0.1	± 0.15
10-50	± 0.1	± 0.15	± 0.2
未标注的公差按一般标准计算			

深圳市精拓金电子有限公司

单位 UNITS	司 MM	制图 DRAWING	客户料号 PRODUCT PART NO.	912-121A101AD10200		
比例 SCALE	1:1	审核 CHKD	产品名称 PRODUCT NO.	AF10.6短体前两脚无边铁壳PBT白胶8.2DIP		
日期 DATE	2014/04/23	核准 APPD	角法 VIEW	<table border="1"> <tr> <td>版本 VER</td> <td>A0</td> </tr> </table>	版本 VER	A0
版本 VER	A0					