
本公司智慧財產,未經同意不得複製

DAILYWELL copyright, may not be used without permission from DAILYWELL



SWITCH FUNCTION


	PART NO.	PART NAME	Q'TY
1	MNU-2M01	10-48 INCH NUTS	2
2	MNU-2M03	LOCKING WASHER	1


FILE NAME:HARDWARE-0003

		CONTACT PLATING	TERMINAL PLATING	RATINGS	
Q		Silver	Q = Silver		
Ī	S	Silvei	S = Silver,pure-tin	3 Amps @120 VAC or 28 VDC	
	C	Gold over Silver	C = Gold over silver	1 Amps @250 VAC	
	K	Gold over Sliver	K = Gold over silver,pure-tin		
	R	Gold	R = Gold	0.4 Volt-Amps(VA) max. @20V max.	
	G	Oold	G = Gold,pure-tin	(AC or DC)	


德利威電子股份有限公司

	BAILT WELL ELECTRONIOS GO., ETB.						
2	TITLE 圖名	Sub - Miniature Toggle Switches			SIZE 圖紙	A4	
	DWG NO.	0140074541440505			UNIT	inch	
	圖號	2MS3T4B1M1QES-5		單位	mm		
	REV.	۸	DATE	ALIC -	03 - 2016	SHEET	1 of 1
	版本	Α	日期	AUG - 03 - 2016		張數	
	CHECKED BY	陳燈財		DRAWN BY	IRENE		
	審核			製圖	IKEN	1E	









SOLDER LUG

SPECIFICATIONS

MECHANICAL LIFE: 30,000 make-and-break cycles. CONTACT RESISTANCE: 20 m \Omega max, initial @ 2-4VDC

100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000 M Ω min.

DIELECTRIC STRENGTH: 1,000 Vrms min.@sea level.

OPERATING TEMPERATURE: -30°C to 85°C.

MATERIALS

CASE - Diallyl phthalate(DAP)(UL94V-0) **ACTUATOR - Brass, chrome plated BUSHING** - Brass, nickel plated **HOUSING - Stainless Steel TERMINALS -** Copper alloy.

CONTACT - Brass. RoHS & Lead Free

	符號	原尺寸	修改後尺寸	變更日期	」SCALE (比例): 3:2	
1	A				(* =)* 4/	\vdash
2	B				TOLERANCE (公差): 0.00 mm ± 0.25mm	
3	0				0.0 mm ± 0.40mm	
4	\bigcirc				ANGULAR: ± 5°	CI
5	(E)				FILE NAME: 2MSP0984	.

DAILYWELL

德利威電子股份有限公司

版本: C

表單編號: QR-0507