

This document was generated on 09/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 5050060812

Status: Active

Overview: SlimStack Board-to-Board Connectors

Description: SlimStack Board-to-Board Plug, 0.40mm Pitch, Battery Series, 0.75mm Mated Height,

2.50mm Mated Width, 8 Circuits, 6.0A

Documents:

3D Model Packaging Specification 5050069200-200 (PDF)

3D Model (PDF)
Drawing (PDF)
Drawing (PDF)
Drawing (PDF)

Product Specification 5050040000-003 (PDF)

RoHS Certificate of Compliance (PDF)

Application Specification 5050040000-A00 (PDF)

Reference Guide (PDF)

General

Product Family PCB Headers
Series 505006
Application Board-to-Board

Comments * 6A of current per circuit is applicable if the circuit is

constructed by two power pins via a PWB/FPC circuit

Overview SlimStack Board-to-Board Connectors

Product Name SlimStack
Series Name Battery

UPC 191128441100

Physical

(p)ower-(s)ignal Configuration 4p - 4s Breakaway No Circuits (Loaded) 8 Circuits (maximum) 8 Color - Resin Black Durability (mating cycles max) 10 Glow-Wire Capable No Lock to Mating Part Yes Mated Height 0.75mm Mated Width 2.50mm Material - Metal Copper Alloy Material - Plating Mating Gold

Material - Plating Mating Gold Material - Plating Termination Gold

Material - Resin Liquid Crystal Polymer

Net Weight5.410/mgNumber of Rows2OrientationVerticalPCB LocatorNoPCB RetentionYes

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

O.40mm

O.100µm


O.050µm

No

Temperature Range - Operating -40° to +85°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 0.3A, 3.0A* Voltage - Maximum 50V AC (RMS)/DC



EU ELV

Not Relevant

EU RoHS China RoHS

Compliant REACH SVHC

Not Contained Per - D(2020)4578-DC (25

June 2020)

<u>Halogen-Free</u>

<u>Status</u>

Low-Halogen

For more information, please visit Contact US

China ROHS Green Image
ELV Not Relevant
ROHS Phthalates Not Contained

Search Parts in this Series

505006 Series

Mates With

SlimStack Battery (6.0A) Receptacle 505004

Material Info

Reference - Drawing Numbers

Application Specification
Packaging Specification
Product Specification
Sales Drawing

5050040000-A00 5050069200-200 5050040000-003 SD-505006-005, SD-505006-006

This document was generated on 09/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION