



3D VIEW



FLEX LAYER



ECT CONNECTOR

Part NO.	Dimensions(mm)	
	A	B
AT245DBV-L50	50.00	30.00
AT245DBV-L100	100.00	80.00
AT245DBV-L150	150.00	130.00
AT245DBV-L200	200.00	180.00
AT245DBV-L250	250.00	230.00
AT245DBV-L300	300.00	280.00

NOTES:

- MATERIAL:  
 FLEX: SEE FLEX LAYER  
 CABLE:  $\phi$  1.13mm; COLOR: BLACK  
 CONNECTOR: OD1.13, 2.5H ECT CONNECTOR(GOLD PLATING)
- SOLDER MASK COLOR: BLACK
- CAN'T LIFT UP CABLE IN VERTICAL DIRECTION
- APPLICATION SPEC REFER TO AS OF AT245DBV-L100
- PRODUCT SPEC REFER TO PS OF AT245DBV-L100
- PACKAGING SPEC REFER TO PK OF AT245DBV-L100

A0	NEW RELEASE	2020.11.23
REV	DESCRIPTION	DATE

**CJTconn** CHANGJIANG CONNECTORS CO.,LTD.

Unit mm	Scale 1.5:1	Sheet 1 of 1	TITLE <b>2.4/5GHZ WIFI DUAL BAND ANTENNA</b>
DRWN Dengchun Yi	CHK'D Dlankul Wan	APPR Jack Yin	
General Tolerances x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°			
THIRD ANGLE PROJECTION			DRAWING NO. <b>AT245DBV-L</b>
			REV A0