




Position(位数)	1P	
PART NO.	凸柄(P)	EM-01KP
盖子/黑色(K)	短柄(S)	EM-01KS



NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance:  $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 800gf Max
- 5.Mechanical Life: 3,000 Cycles
- 6.Operating Temperature range  $-20^{\circ}\sim+70^{\circ}\text{C}$
- 7.Ambient Humidity used:  $\leq 85\%RH$

④	Terminal	—	2	Phosphor bronze	Au Plating	—
③	Base	—	1	PBT	Black	—
②	Cover	—	1	PBT	Black	—
①	Keystoke	—	1	PBT	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD				
DRAWN	J.X.Zhang	2020/05/08						
CHECKED				TITLE:	MULTIFUNCTIONAL SWITCHES			
APPROVALS				PART NO.	EM-01□□			
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm		
			10~30	±0.20				
			5~10	±0.15				
			~ 5	±0.10				
				SCALE: 1:1	PROJ:			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.