





HSF

Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE±0.05)

NOTES:
 Rated Current: 3.0AMP.
 Contact Resistance: 20mΩ Max.
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min.
 Operation Temperature: -40℃ to +105℃
 Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: PA9T+33%G.F UL94V-0 BK



Ordering Information

1125-11 XX XX S XXX C 0 XX

No. of Pins: 02-40
 Contact Plating: G0=Gold Flash, G3=10u"Gold, G4=15u"Gold, G5=30u"Gold, S0=Gold Flash/Tin, S3=10u"Gold/Tin, S4=15u"Gold/Tin, S5=30u"Gold/Tin, SN=Tin, SM=Matte Tin
 Pin Length: L=A+B+2.5, Standard: 085=8.5, 095=9.5, 105=10.5, 116=11.6, 118=11.8, 135=13.5
 Insulator Material: C=PA9T
 Packing: 0=PE Bag, T=Tube
 Series No.: 01-99

Item	Pin Length	A	B	Mating
Standard	8.50	3.00	3.00	2135
	9.50	3.00	4.00	2145
	10.50	3.00	5.00	2150
	11.60	3.00	6.10	2171 2185
	11.80	2.40	6.90	2171 2185
Alternate				

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.	TITLE:
A3	2018/06/02	Cancel PBT & Modify P/N	A3	x.x	±0.40	OPERATION	Surong Xu	2018/06/02	UNIT	mm [inch]	1125-11XXXXSXXXC0XX	PH2.54 SINGLE ROW S/T H=2.5
A2	2018/01/22	Modify P/N	A2	x.xx	±0.25	CHECK	CHECK	DATE	SIZE	A4		
A1	2016/02/19	MODIFY DRAWING	-----	x.xxx	±0.15	APPROVE	APPROVE	DATE	SHEET	1/1		
A0	2012/05/17	NEW	-----	Angle	± 3°				PROJ.	☯		
											Customer NO.	

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com