







ABIDE BY ROHS



■ Specification :

- 1. Rating :DC30V 0.1A ; Circuit: COM-NO
- 2. Contact Resistance : 100mΩ Max
- 3. Insulation Resistance :100MΩ Min(DC250V)
- 4. Withstand Voltage :AC500V(50-60Hz)for 1 minute
- 5. Operation Force : 65±15gf
- 6. Releasing Force :25gf(Min)
- 7. Operating Position : 6.90±0.2 mm
- 8. Mechanical Life : 10,000,000 Cycles(min)



| 8 | Contact | 1 | Composite gold | Natural | | |
|------|--------------|---------|----------------|----------------|-----------|--------|
| 7 | Shrapnel | 1 | Copper Alloy | Natural | | |
| 6 | Keystoke | 1 | POM | Coffee | UL94HB | |
| 5 | Cover | 1 | PBT | Black | UL94HB | |
| 4 | Base | 1 | PBT | Black | UL94HB | |
| 3 | Nc Terminal | 3 | BRASS | Plating Silver | | |
| 2 | No Terminal | 2 | BRASS | Plating Silver | | |
| 1 | Com Terminal | 1 | BRASS | Plating Silver | | |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |

| | | | |
|----------------|---------|------------|---|
| APPROVALS | | DATE | 东莞市凯华电子有限公司 DONGGUAN CITY KAIHUA ELECTRONICS CO.,LTD |
| DRAWN | L.Zhang | 2015.11.05 | |
| CHECKED | | | |
| APPROVALS | | | |
| | | | TITLE: 10M Micro Switch |
| | | | Customer No. |
| | | | PART NO. CM126603D07 |
| TOLERANCES ARE | | ANGLE | UNIT: mm |
| 30 | ±0.30 | | SCALE: 1:1 |
| 10 | ±0.20 | | PROJ: |
| 0.5 | ±0.15 | ±2° | DRAWING NO. KHA-MI266-003EN |
| 0.2 | ±0.10 | | SHEET 1 OF 1 |

| | C | 2015.11.05 | REDRAW | L.Zhang | | |
|---------|------|------------|--------------|----------|--------|--------|
| | A | 2013.12.11 | NEW | Shixijun | | |
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |