


REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

Specifications

Current Rating: 1.5 Ampere
 Insulation Resistance: 1000M Ω Min.
 Withstanding Voltage: 500V AC
 Contact Resistance: 20m Ω Max.
 Temperature Range—Operating: -40°C to +105°C

Materials

Housing: PBT UL 94V-0
 Terminal: Phosphor Bronze/All or Over 50'' Ni



 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 26/JUN/13	PART NO. FR-1YF-05	ITEM NO. FR-1YF-05	 Leader Of Industry	
	DESIGN UNITS Inch (metric)	X.±.012(0.30) X.X±.008(0.20)	X.±5' .X'±2'	CHECKED BY JACOB	DATE 26/JUN/13	TITLE .079''(2.00mm) PITCH Conn		REV 0
SCALE 5:1	SIZE A4	X.XX±.006(0.15) X.XXX±.004(0.10)	.XX'±1' .XXX'±0.5'	DRAWN BY CHERRY	DATE 26/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		