



### 规格说明: Specifications:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触电阻: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘电阻: Insulation Resistance:  
1000MEGA ohms MIN

### 物理性能: Mechanical:

1. 插拔力: Connector Mate and Umate Force  
Mate force: 3.57kgf(MAX)  
Umate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention  
1.0kgf(MIN)

### 1. 塑胶: Housing:

Hing Temperature Ternmaplastics,

### 2. 端子: Contact: Copper Alloy C2680

### 3. 外壳: Shell: Copper Alloy C2680/SPCC

1. 端子: Contact: Plated Gold in Mating Area  
Tin On Solder Tails

端子四周镀50U”(MIN)锡,镀金区域镀100—200U”镀金1U”

铜壳四周镀80U”(MIN)锡

Nickel Plating

产品图 MANUFACTURE DWG		深圳市金航标电子有限公司		WWW.BDS666.COM	
公差一览表 TOLERANCE UNLESS OTHERWISE	.X±0.15	X.±5°	KH-AF180ZJ-17.5-JB	0755-83044319	
日期 DATE		单位 UNIT	MM	制图 DRAWING	
审核 CHECKED		比例 SCALE	1:1	设计 DESIGN	
批准 APPROVE		画法 VIEW			
XXXX±0.02	.XX±1°			DWG NO.	品名 NAME
					版本 VER
					结构特征
					页码 SHEET